




PosiMixer®

Disposable Motionless Mixers



Disposable mixers – simply attach, dispense and dispose

- Spiral mixing action thoroughly mixes two-component materials
- No solvent flushing means less mess and reduced disposal expenses
- Rugged, chemical-resistant mixer housing and mixing elements
- Easily adapts to fit most meter, mix and dispense systems

PROVEN QUALITY. LEADING TECHNOLOGY.



Get a superior, uniform mix — every time

How PosiMixer works

Input

Two materials flow through a series of alternating right and left helical elements oriented at 90 degrees to one another.

Mixing

As reactive materials are metered through the mixer, they are divided and folded over each other again and again in a churning, mixing action.

Output

When materials reach the mixer outlet, they are thoroughly mixed into a homogenous material.



Mixers for any application

- Sizes range from 0.125 in (3 mm) to 0.75 in (19 mm) diameter
- Various element configurations are available to ensure proper blending of plural-component materials
- Combo packages are available – these feature different size elements in the same housing for difficult-to-mix materials



Ordering Information

Provide your part specifications and we will suggest the ideal mixer solution best suited for your application.

Contact us today!

To receive product information or to request a hands-on demonstration, call 877-844-7226 or visit us online at www.graco.com.

Materials		Accessories
Epoxies	Polysulfides	Adapters
Urethanes	Acrylics	Retaining caps
Silicones	Other two-component reactive resins	Shrouds
Polyesters		Luer lock needles